

934008MED8

















M






















































Assortimento EVAWAVE per
cassettiera - 155 pezzi

Peso (kg) : 17.69



97392MRE01

			2335M	5.5 , 6 , 7 , 8 , 9 , 10 , 11 , 12 , 13 , 14
			2771G	277155G
			2745	2745
			2221	222102, 222104 (55, 100 mm)
			2571	257145
		 	2142	2142

		213312DF	213312DF
		2178DF	2178DF
		2792	2792
			4335M 10 , 11 , 12 , 13 , 14 , 15 , 16 , 17 , 18 , 19 , 21 , 22 , 24 , 27 , 30 , 32
			4235M 8 , 9 , 10 , 12 , 13 , 14 , 15 , 16 , 17 , 18 , 19
			4375M E10 , E12 , E14 , E16 , E18
			4035 H6 , H8 , H10
			4033 T30 , T40 , T50 , T55
			4049 M8 , M9 , M10 , M12
			4026 M14
			4036 M8 , M10 , M12
			402B M16 , M18
		4771G	477110G
		4251	425105 , 425110 (125 , 250 mm)
		4791	4791
			1025P PH1 , PH2 , PH3
			1025Z PZ1 , PZ2 , PZ3
			1025H H3 , H4 , H5 , H6
			1025U T7H , T8H , T9H , T10H , T15H , T20H , T25H , T27H , T30H , T40H
			
912D19MRE1			
		1062	6 , 7 , 8 , 9 , 10 , 11 , 12 , 13 , 14 , 15 , 16 , 17 , 18 , 19 , 20 , 21 , 22 , 23 , 24


931110MRE

1421
PH1 x 80, PH.2 x100, PH.3 x 150, PH.2 x 38

1422
3 x 75, 4 x 100, 5.5 x 125, 6.5 x 38, 6.5 x 150, 8 x 175


990222MRE01

1120MR
H1.5, H2, H2.5, H3, H4, H5, H6, H7, H8

1147R
T10H, T15H, T20H, T25H, T27H, T30H, T40H, T45H, T50H

6111
611107

6517C
651710C

6211
621106

6311
631106

942134GPE





67HS
67HS07

67SS
67SS07

67HB
67HB07

67SB
67SB07


990118PRE

	761	7610405 (Ø 4 mm)
	762	7621706, 7622007 (17, 20 mm)
	764	7640305, 7640406, 7640565, 7640607 (Ø 3, Ø 4, Ø 5, Ø 6 mm)
	78210S	7821300S